PRETREATmaker Basic





TO UPGRADE YOUR PRETREATMENT CAPABILITIES, CONTACT BROTHER DTG at 866-750-2542 or visit BrotherDTG.com.





Spraying area	15.7 × 17.7" (40 × 45 cm)
Spraying method	Nozzle is moving over the table (inside)
Table length	24.4" (62 cm)
Spray direction	Uni / Bi-Directional
Nozzles	1 Nozzle
Number of bottles	Two Pretreat (2 Liter Bottles), One Water (2 Liter), One Waste (2 Liter)
Motor	Stepper Motor
Pumps	One pump
Dimensions	L 27.5" × W 20.5" × H 22.0" (L 70 × W 52 × H 56 cm)
Dimensions (transport)	L 31.5" × W 22.8" × H 28.7" (L 80 × W 58 × H 73 cm)
Weight	84 lbs. (38 kg)
Weight (transport)	104 lbs. (47 kg)
Connection	220/230 or 110/120 VAC (automatic switch)
Consumption	150 W
Operating pressure (precoating)	max. 7 bar
Included in delivery	replacement nozzle, replacement filter and ultrasound cleaner
Additional characteristics	zinc- and powder-coated housing











- 1. Schulze Pretreat Cleaner 807068
- 2. Nozzle (green) TP9501EVS
- 3. Filter 807015

- 4. 0-ring washer 803368
- 5. Quick exchange cap 803368

